

# **LSH 20**

# Primary Li-SOCI, cell

High power density 3.6 V D-size spiral cell

Saft's LSH 20 cell is ideally suited for longterm applications (typically from 5 to 20+ years), featuring high drain / high pulses currents.

#### **Benefits**

- High power / high energy densities (65) W/kg and 468 Wh/kg)
- · High voltage response, stable during most of the lifetime of the application
- · Wide operating temperature range (-60°C/+85°C)
- · Low self-discharge rate, compatible with long operating life (less than 3% per year of storage, at + 20°C, after 1 year)
- · Superior resistance to corrosion
- · Low magnetic signature

#### **Key features**

- Spiral construction
- · Built-in safety vent
- · Finishing top with 5 A fuse
- · Hermetic construction with glass-tometal seal
- Stainless steel can
- · Non-flammable electrolyte
- · RoHS and REACH compliance
- · Made in France

## Designed to meet all major quality, safety and environment standards

- · Safety: UL 1642, IEC 60086-4
- Transport: UN 3090 and UN 3091
- · Quality: ISO 9001, Saft Excellence System, continuous program

### **Typical applications**

- Utility Metering
- Tracking systems
- Dataloggers
- · Alarms and security
- · Wireless sensors
- · Military radios

**NATO Stock Number** 6135 14 440 1213



Electrical characteristics	
Nominal capacity (under 14 mA, +20°C, 2.0 V cut-off) <sup>3</sup>	13 Ah
Open circuit voltage (at +20°C)	3.67 V
Nominal voltage (at 2 mA, + 20°C)	3.6 V
Nominal energy	47 Wh
Pulse capability <sup>4</sup>	Up to 4 A
Maximum recommended continuous current	1.8 A
For battery sizing, consult Saft	
Operating conditions	
Operating temperature range <sup>5</sup>	-60°C / +85°C (-76°C / +185°F)
Storage temperatures (max recommended) <sup>6</sup>	+30°C (+86°F)
Physical characteristics <sup>2</sup>	
Diameter (max)	33.26 mm (1.31 in)
Height (max)	61.31 mm (2.41 in)
Typical weight	100 g (3.5 oz)
Li metal content	approx. 3.8 g
Termination suffix	
CN, CNR	Radial tabs
2 PF, 3 PF, 3 PF RP, 4 PF	Radial pins
CNA	Axial leads
FL	Flying leads
Other configurations upon request	






Steeved cell. \*Dependent upon current drain, temperature, cut-off and cell orientation. \*Under 4 A / 0.1 second pulses, drained every 2 minutes at + 20°C from undischarged cells during 24 h, with 10 µA base current, yield voltage readings above 3.0 V after initial stabilisation. The readings may vary according to the pulse characteristics, the temperature, and the cell's previous history. Fitting the cell with a capacitor may be recommended in severe conditions or for high pulse currents. Consult Saft. \*Toperation above ambient temperature may lead to reduced capacity and lower voltage readings. Consult Saft. \*For more severe conditions, consult Saft.



# **LSH 20**

# Primary Li-SOCI, cell



Dimensions in mm

# 6.6Ω/0.52 A 35Ω/100mA 250Ω/14.3mA 1.8 A 50Ω/71mA 10 15 Discharged capacity (Ah) Voltage plateau versus current and temperature (at mid-discharge) 4.0 Cell voltage [V] 3.0

# 2.5 2.0 0.001 Discharge current [A]


## **Storage**

· The storage area should be clean, cool (preferably not exceeding +30°C), dry and ventilated.

## Warning

- Fire, explosion and severe burn hazard.
- · Do not recharge, short circuit, crush, disassemble, heat above 100°C (212°F), incinerate, or expose contents to water.
- · Do not solder directly to the cell (use tabbed cell versions instead).
- · Do not remove the cells from their original packing before use.
- · Do not store the cells in bulk to avoid accidental short circuiting.
- · Do not mix new and used cells or cells from different origins.
- · Mind the polarities of the cell.





26, quai Charles Pasqua 92300 Levallois-Perret - France www.saft.com

Typical discharge profiles at +20°C

3.5

2.5

2.0

Cell voltage [V] 3.0

Saft, a subsidiary of TotalEnergies S.A.S. au capital de 26 724 876 € R.C.S. Nanterre 481 480 465

Document N° 31015-2-0923 Edition: September 2023 Data in this document is subject to change without notice and becomes contractual only after written confirmation Photo credits: © Saft